Geiger Chemie GmbH Jahnstraße 46 78234 Engen www.geiger-chemie.de Telefon (07733) 99 31-0 Fax (07733) 99 31-30

eMail: info@geiger-chemie.de



Remover for Woodchip Wallpaper

For easy removal of painted woodchip wallpapers and all wallpapers that are difficult to remove

The product removes all woodchip wallpapers (also if they have been Scope of application:

coated several times), without using the spiked roller or sand paper, etc.

And it can also be used to remove wallpapers that are difficult to remove,

such as textile wallpapers or Venyl wallpapers.

Can be applied without the spiked roller, also for woodchip wallpapers Properties:

> that have been coated several times = significant shorter processing time. Extremely high detachment forces through special additives = no draining

on the wallpaper

The product can be applied with the garden irrigation nozzle.

Technical specifications: Raw material base: aqueous solution of surfactants and alcohol

Make-up ratio: 250 ml in 5 to 6 l water

Consumption: 100 ml of the remover for woodchip wallpaper are suffi-

cient for 20 - 25 m²

To remove painted woodchip wallpapers add 250 ml of the remover to 5 Processing:

> to 6 litre warm water. For other wallpapers add 250 ml to 10 litre warm water. Use a ceiling swab, sponge or garden irrigation nozzle to apply the remover generously in run direction of the wallpaper, and allow it approx. 15 minutes to react. The application can be repeated, if required.

Then remove the wallpapers strip by strip.

Always clean the tools thoroughly with water immediately after use.

Identification: Please refer to the EC safety data sheet for the pertinent information.

Storage property: Store the product in a cool, dark and dry place.

Other: Always read the label and product information before use.

> Use warm or hot water to increase the effect. Water-repellent wallpapers must be slightly roughened with a spiked roller before applying the sol-

vent.

Container sizes: Bottle with 250 ml

> Bottle with 500 ml Bottle with 1,000 ml Jerrican with 5 l Jerrican with 10 L